

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252839

Luminaire Tested: P3AS20R559030D010 E3DLP1MW

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252839
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R559030D010 E3DLP1MW
Description: 3in Adjustable LED luminaire with, R55 optic, 3000K CCT AND, 90CRI , E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1229.0 lumens
Efficiency: N/A
Efficacy: 42.7 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252839
CATALOG NUMBER: P3AS20R559030D010 E3DLP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P1252839
 CATALOG NUMBER: P3AS20R559030D010 E3DLP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	137.5	11.2
10°-20°	329.5	26.8
20°-30°	349.0	28.4
30°-40°	235.8	19.2
40°-50°	103.4	8.4
50°-60°	37.0	3.0
60°-70°	21.7	1.8
70°-80°	11.3	0.9
80°-90°	3.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	816.1	66.4
0°-40°	1051.9	85.6
0°-60°	1192.3	97.0
0°-90°	1229.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1229.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1525	
5°	1481	137
15°	1189	330
25°	765	349
35°	375	236
45°	127	103
55°	37	37
65°	22	22
75°	10	11
85°	3	4
90°	0	



TEST NUMBER: P1252839
CATALOG NUMBER: P3AS20R559030D010 E3DLP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1524.7
2.5°	1512.8
5°	1480.8
7.5°	1428.4
10°	1360.9
12.5°	1279.8
15°	1188.7
17.5°	1087.3
20°	982.7
22.5°	872.9
25°	764.9
27.5°	658.5
30°	557.2
32.5°	460.9
35°	374.8
37.5°	297.2
40°	231.3
42.5°	173.9
45°	126.6
47.5°	92.9
50°	67.5
52.5°	47.3
55°	37.1
57.5°	33.8
60°	28.7
62.5°	25.3
65°	21.9
67.5°	18.6
70°	15.2
72.5°	13.5
75°	10.1
77.5°	8.4
80°	6.8
82.5°	5.1
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)