

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1252887

Luminaire Tested: P3AS20R659030D010 E3DL1WMH

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1252887
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS20R659030D010 E3DL1WMH
Description: 3in Adjustable LED luminaire with, R65 optic, 3000K CCT AND, 90CRI , E3DL1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1695.0 lumens
Efficiency: N/A
Efficacy: 58.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 28.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1252887
CATALOG NUMBER: P3AS20R659030D010 E3DL1WMH

Luminous Intensity Polar Plot





TEST NUMBER: P1252887

CATALOG NUMBER: P3AS20R659030D010 E3DL1WMH

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.5	9.9
10°-20°	436.3	25.7
20°-30°	509.9	30.1
30°-40°	356.4	21.0
40°-50°	156.9	9.3
50°-60°	34.9	2.1
60°-70°	17.8	1.0
70°-80°	10.7	0.6
80°-90°	3.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1114.7	65.8
0°-40°	1471.1	86.8
0°-60°	1662.9	98.1
0°-90°	1695.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1695.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1823	
5°	1794	168
15°	1568	436
25°	1124	510
35°	566	356
45°	198	157
55°	29	35
65°	19	18
75°	10	11
85°	3	4
90°	0	



TEST NUMBER: P1252887
CATALOG NUMBER: P3AS20R659030D010 E3DL1WMH

CANDELA DISTRIBUTION (FULL):

	0°
0°	1822.9
2.5°	1816.2
5°	1794.2
7.5°	1757.0
10°	1706.3
12.5°	1643.8
15°	1567.8
17.5°	1474.9
20°	1371.8
22.5°	1255.3
25°	1123.5
27.5°	984.9
30°	839.7
32.5°	699.4
35°	566.0
37.5°	449.4
40°	346.3
42.5°	261.9
45°	197.7
47.5°	145.3
50°	91.2
52.5°	47.3
55°	28.7
57.5°	25.3
60°	22.0
62.5°	20.3
65°	18.6
67.5°	15.2
70°	13.5
72.5°	11.8
75°	10.1
77.5°	8.4
80°	6.8
82.5°	5.1
85°	3.4
87.5°	1.7
90°	0.0

(END OF REPORT)