

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1269420

Luminaire Tested: P3AS09R309740DE010 E3DLP1H

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1269420
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-13)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R309740DE010 E3DLP1H
Description: 3in Adjustable LED luminaire with, R30 optic, 4000K CCT AND, 97CRI , E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 457.0 lumens
Efficiency: N/A
Efficacy: 41.2 lumens/watt
Spacing Criteria (0/90/45): 0.66 / 0.66 / 0.7
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 11.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1269420
CATALOG NUMBER: P3AS09R309740DE010 E3DLP1H

Luminous Intensity Polar Plot





TEST NUMBER: P1269420
 CATALOG NUMBER: P3AS09R309740DE010 E3DLP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.2	13.8
10°-20°	136.8	29.9
20°-30°	124.5	27.2
30°-40°	75.2	16.5
40°-50°	30.2	6.6
50°-60°	13.4	2.9
60°-70°	8.1	1.8
70°-80°	4.4	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	324.5	71.0
0°-40°	399.8	87.5
0°-60°	443.3	97.0
0°-90°	457.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	457.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	712	
5°	687	63
15°	497	137
25°	271	124
35°	118	75
45°	37	30
55°	15	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1269420
CATALOG NUMBER: P3AS09R309740DE010 E3DLP1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	712.2
1°	711.5
2°	708.6
3°	703.7
4°	696.6
5°	687.4
6°	676.0
7°	664.0
8°	648.4
9°	630.7
10°	612.3
11°	591.0
12°	568.3
13°	545.6
14°	520.8
15°	496.7
17.5°	433.7
20°	374.2
22.5°	318.9
25°	270.7
27.5°	226.8
30°	187.8
32.5°	151.6
35°	118.3
37.5°	90.7
40°	68.0
42.5°	49.6
45°	36.8
47.5°	27.6
50°	20.6
52.5°	16.3
55°	14.9
57.5°	12.8
60°	11.3
62.5°	9.2
65°	7.8
67.5°	7.1
70°	5.7
72.5°	5.0
75°	4.3
77.5°	3.5
80°	2.1
82.5°	1.4
85°	1.4
87.5°	0.7



TEST NUMBER: P1269420
CATALOG NUMBER: P3AS09R309740DE010 E3DLP1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0

(END OF REPORT)