

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1282656

Luminaire Tested: P3AS09R15B2750DE010 E3DLD1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1282656
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15B2750DE010 E3DLD1WMH_5000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R15 optic, 5000K CCT AND, 80CRI , E3DLD1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 494.0 lumens
Efficiency: N/A
Efficacy: 37.7 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 13.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1282656
CATALOG NUMBER: P3AS09R15B2750DE010 E3DLD1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1282656

CATALOG NUMBER: P3AS09R15B2750DE010 E3DLD1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	50.8	10.3
10°-20°	119.1	24.1
20°-30°	131.2	26.6
30°-40°	98.3	19.9
40°-50°	50.9	10.3
50°-60°	21.1	4.3
60°-70°	13.1	2.6
70°-80°	7.3	1.5
80°-90°	2.1	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	301.1	61.0
0°-40°	399.4	80.9
0°-60°	471.5	95.4
0°-90°	494.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	494.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	568	
5°	551	51
15°	427	119
25°	287	131
35°	156	98
45°	64	51
55°	22	21
65°	13	13
75°	7	7
85°	2	2
90°	0	



TEST NUMBER: P1282656
CATALOG NUMBER: P3AS09R15B2750DE010 E3DLD1WMH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	568.2
1°	568.9
2°	567.0
3°	563.2
4°	557.6
5°	550.7
6°	542.0
7°	532.6
8°	521.3
9°	509.4
10°	497.5
12.5°	463.1
15°	427.4
17.5°	391.8
20°	356.7
22.5°	321.0
25°	287.3
27.5°	253.5
30°	219.7
32.5°	186.5
35°	155.8
37.5°	129.5
40°	105.8
42.5°	83.9
45°	63.8
47.5°	48.2
50°	36.3
52.5°	26.9
55°	21.9
57.5°	19.4
60°	16.9
62.5°	15.0
65°	13.1
67.5°	11.3
70°	10.0
72.5°	8.1
75°	6.9
77.5°	5.6
80°	4.4
82.5°	3.1
85°	1.9
87.5°	0.6
90°	0.0

(END OF REPORT)