

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1285415

Luminaire Tested: P3AS13R50B2750DE010 E3DLP1LI_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1285415
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50B2750DE010 E3DLP1LI_4000K
Description: 3in Adjustable Boosted Cyan Tunable White LED luminaire with, R50 optic, 4000K CCT AND, 80CRI , E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 568.0 lumens
Efficiency: N/A
Efficacy: 29.7 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 19.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1285415
CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1LI_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1285415

CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1LI_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.7	11.9
10°-20°	159.0	28.0
20°-30°	162.7	28.6
30°-40°	103.2	18.2
40°-50°	41.1	7.2
50°-60°	16.6	2.9
60°-70°	10.6	1.9
70°-80°	5.5	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	389.4	68.5
0°-40°	492.5	86.7
0°-60°	550.2	96.9
0°-90°	568.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	568.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	753	
5°	730	68
15°	574	159
25°	358	163
35°	163	103
45°	50	41
55°	18	17
65°	11	11
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1285415
CATALOG NUMBER: P3AS13R50B2750DE010 E3DLP1LI_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	753.4
2.5°	748.0
5°	730.3
7.5°	702.6
10°	665.7
12.5°	621.9
15°	574.3
17.5°	522.0
20°	467.4
22.5°	412.8
25°	357.5
27.5°	302.1
30°	250.6
32.5°	204.5
35°	163.0
37.5°	127.6
40°	96.9
42.5°	71.5
45°	50.0
47.5°	33.8
50°	24.6
52.5°	20.8
55°	18.5
57.5°	16.1
60°	13.8
62.5°	12.3
65°	10.8
67.5°	9.2
70°	7.7
72.5°	6.2
75°	5.4
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)