

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1289663

Luminaire Tested: P3AS05R40W2N902765DE010 E3DLP1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1289663
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R40W2N902765DE010 E3DLP1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 291.1 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1289663
CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1289663

CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	37.4	12.9
10°-20°	87.4	30.0
20°-30°	82.4	28.3
30°-40°	47.6	16.4
40°-50°	19.0	6.5
50°-60°	8.4	2.9
60°-70°	5.2	1.8
70°-80°	2.7	0.9
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	207.2	71.2
0°-40°	254.9	87.6
0°-60°	282.2	97.0
0°-90°	291.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	291.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	413	
5°	403	37
15°	317	87
25°	180	82
35°	75	48
45°	23	19
55°	9	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1289663
CATALOG NUMBER: P3AS05R40W2N902765DE010 E3DLP1LI_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	413.2
2.5°	410.8
5°	403.3
7.5°	389.4
10°	371.2
12.5°	346.7
15°	317.3
17.5°	284.5
20°	248.8
22.5°	213.1
25°	179.9
27.5°	149.0
30°	120.8
32.5°	96.3
35°	74.9
37.5°	56.7
40°	42.4
42.5°	31.7
45°	23.4
47.5°	17.0
50°	12.7
52.5°	10.3
55°	9.1
57.5°	8.3
60°	7.1
62.5°	5.9
65°	5.2
67.5°	4.4
70°	4.0
72.5°	3.2
75°	2.4
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)