

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1290739

Luminaire Tested: P3AS05R60W2N902750DE010 E3DLP1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1290739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R60W2N902750DE010 E3DLP1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 261.0 lumens
Efficiency: N/A
Efficacy: 44.2 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1290739
CATALOG NUMBER: P3AS05R60W2N902750DE010 E3DLP1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1290739

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3DLP1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	27.3	10.5
10°-20°	66.4	25.5
20°-30°	72.9	27.9
30°-40°	53.1	20.3
40°-50°	25.1	9.6
50°-60°	8.2	3.1
60°-70°	4.7	1.8
70°-80°	2.5	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	166.7	63.8
0°-40°	219.7	84.2
0°-60°	253.1	97.0
0°-90°	261.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	261.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	302	
5°	294	27
15°	239	66
25°	160	73
35°	85	53
45°	32	25
55°	8	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1290739

CATALOG NUMBER: P3AS05R60W2N902750DE010 E3DLP1WMH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	301.6
2.5°	299.9
5°	293.8
7.5°	284.4
10°	271.9
12.5°	256.8
15°	239.2
17.5°	220.2
20°	200.1
22.5°	179.7
25°	159.6
27.5°	139.5
30°	120.5
32.5°	102.2
35°	84.6
37.5°	68.9
40°	54.5
42.5°	42.0
45°	31.6
47.5°	23.0
50°	15.8
52.5°	10.4
55°	8.2
57.5°	7.2
60°	6.5
62.5°	5.4
65°	4.7
67.5°	3.9
70°	3.2
72.5°	2.9
75°	2.5
77.5°	1.8
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)