

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291209

Luminaire Tested: P3AS05R65W2N902765DE010 E3DLP1H\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1291209  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS05R65W2N902765DE010 E3DLP1H\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,  
E3DLP1H TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 277.9 lumens  
Efficiency: N/A  
Efficacy: 47.1 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 5.9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1291209  
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLP1H\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1291209

CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLP1H\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	29.1	10.5
10°-20°	70.4	25.3
20°-30°	77.8	28.0
30°-40°	56.5	20.3
40°-50°	26.5	9.5
50°-60°	8.9	3.2
60°-70°	5.1	1.8
70°-80°	2.7	1.0
80°-90°	0.9	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	177.3	63.8
0°-40°	233.9	84.1
0°-60°	269.2	96.9
0°-90°	277.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	277.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	322	
5°	313	29
15°	253	70
25°	171	78
35°	90	57
45°	33	26
55°	9	9
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1291209  
CATALOG NUMBER: P3AS05R65W2N902765DE010 E3DLP1H\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	322.2
2.5°	320.2
5°	313.0
7.5°	302.2
10°	288.2
12.5°	271.7
15°	253.3
17.5°	233.3
20°	212.8
22.5°	191.6
25°	170.7
27.5°	149.5
30°	128.7
32.5°	108.6
35°	90.2
37.5°	73.3
40°	58.1
42.5°	44.5
45°	33.3
47.5°	24.0
50°	16.4
52.5°	11.2
55°	9.2
57.5°	8.0
60°	6.8
62.5°	6.0
65°	5.2
67.5°	4.4
70°	3.6
72.5°	3.2
75°	2.4
77.5°	2.0
80°	1.6
82.5°	1.2
85°	0.8
87.5°	0.4
90°	0.0

(END OF REPORT)