

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291332

Luminaire Tested: P3AS05R70W2N902750DE010 E3DLP1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291332
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS05R70W2N902750DE010 E3DLP1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 2700K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 258.0 lumens
Efficiency: N/A
Efficacy: 43.7 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 5.9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291332
CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DLP1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1291332

CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DLP1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	25.2	9.8
10°-20°	62.3	24.2
20°-30°	71.0	27.5
30°-40°	55.5	21.5
40°-50°	27.3	10.6
50°-60°	8.4	3.2
60°-70°	5.0	1.9
70°-80°	2.7	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	158.5	61.4
0°-40°	213.9	82.9
0°-60°	249.6	96.7
0°-90°	258.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	258.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	276	
5°	270	25
15°	224	62
25°	155	71
35°	89	55
45°	35	27
55°	9	8
65°	5	5
75°	2	3
85°	1	1
90°	0	



TEST NUMBER: P1291332
CATALOG NUMBER: P3AS05R70W2N902750DE010 E3DLP1LI_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	276.0
2.5°	274.5
5°	269.9
7.5°	262.3
10°	251.6
12.5°	239.0
15°	223.9
17.5°	207.8
20°	190.6
22.5°	172.6
25°	155.0
27.5°	137.8
30°	121.3
32.5°	104.8
35°	89.0
37.5°	73.9
40°	59.6
42.5°	46.3
45°	34.8
47.5°	24.4
50°	15.8
52.5°	10.4
55°	8.6
57.5°	7.5
60°	6.5
62.5°	5.7
65°	5.0
67.5°	4.3
70°	3.6
72.5°	2.9
75°	2.5
77.5°	2.2
80°	1.4
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)