

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1291787

Luminaire Tested: P3AS09R15W2N902765DE010 E3DLD1LI_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1291787
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-2)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R15W2N902765DE010 E3DLD1LI_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R15 optic, 3000K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 460.0 lumens
Efficiency: N/A
Efficacy: 51.1 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.82
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1291787
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1LI_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1291787

CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1LI_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	47.3	10.3
10°-20°	110.9	24.1
20°-30°	122.2	26.6
30°-40°	91.5	19.9
40°-50°	47.4	10.3
50°-60°	19.7	4.3
60°-70°	12.2	2.6
70°-80°	6.8	1.5
80°-90°	2.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	280.4	61.0
0°-40°	371.9	80.9
0°-60°	439.0	95.4
0°-90°	460.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	460.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	529	
5°	513	47
15°	398	111
25°	268	122
35°	145	92
45°	59	47
55°	20	20
65°	12	12
75°	6	7
85°	2	2
90°	0	



TEST NUMBER: P1291787
CATALOG NUMBER: P3AS09R15W2N902765DE010 E3DLD1LI_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	529.1
1°	529.7
2°	528.0
3°	524.5
4°	519.2
5°	512.8
6°	504.7
7°	495.9
8°	485.4
9°	474.4
10°	463.3
12.5°	431.2
15°	398.0
17.5°	364.8
20°	332.2
22.5°	298.9
25°	267.5
27.5°	236.0
30°	204.5
32.5°	173.7
35°	145.1
37.5°	120.6
40°	98.5
42.5°	78.1
45°	59.4
47.5°	44.9
50°	33.8
52.5°	25.1
55°	20.4
57.5°	18.1
60°	15.7
62.5°	14.0
65°	12.2
67.5°	10.5
70°	9.3
72.5°	7.6
75°	6.4
77.5°	5.2
80°	4.1
82.5°	2.9
85°	1.7
87.5°	0.6
90°	0.0

(END OF REPORT)