

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292066

Luminaire Tested: P3AS09R20W2N902765DE010 E3DL1H_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292066
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-7)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R20W2N902765DE010 E3DL1H_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 547.0 lumens
Efficiency: N/A
Efficacy: 60.8 lumens/watt
Spacing Criteria (0/90/45): 0.44 / 0.44 / 0.46
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292066
CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DL1H_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1292066

CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DL1H_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	150.5	27.5
10°-20°	214.8	39.3
20°-30°	112.2	20.5
30°-40°	43.4	7.9
40°-50°	14.1	2.6
50°-60°	5.6	1.0
60°-70°	3.7	0.7
70°-80°	2.1	0.4
80°-90°	0.7	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	477.5	87.3
0°-40°	520.9	95.2
0°-60°	540.5	98.8
0°-90°	547.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	547.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1919	
5°	1738	151
15°	770	215
25°	236	112
35°	65	43
45°	17	14
55°	6	6
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1292066
CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DL1H_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1919.2
1°	1915.5
2°	1892.8
3°	1858.0
4°	1804.1
5°	1738.0
6°	1659.8
7°	1573.1
8°	1472.7
9°	1375.0
10°	1269.8
12.5°	1009.3
15°	770.4
17.5°	576.5
20°	428.0
22.5°	317.1
25°	235.7
27.5°	173.9
30°	126.3
32.5°	91.4
35°	65.0
37.5°	47.0
40°	33.3
42.5°	23.8
45°	16.9
47.5°	12.2
50°	9.0
52.5°	6.9
55°	5.8
57.5°	5.3
60°	4.8
62.5°	4.2
65°	3.7
67.5°	3.2
70°	2.6
72.5°	2.6
75°	2.1
77.5°	1.6
80°	1.1
82.5°	1.1
85°	0.5
87.5°	0.5
90°	0.0

(END OF REPORT)