

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292102

Luminaire Tested: P3AS09R20W2N902765DE010 E3DLD1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292102
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R20W2N902765DE010 E3DLD1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3DLD1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 416.0 lumens
Efficiency: N/A
Efficacy: 46.2 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292102
CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DLD1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1292102

CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DLD1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.1	10.1
10°-20°	99.4	23.9
20°-30°	110.4	26.5
30°-40°	84.2	20.2
40°-50°	43.1	10.4
50°-60°	17.7	4.3
60°-70°	11.1	2.7
70°-80°	6.2	1.5
80°-90°	1.8	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	251.9	60.6
0°-40°	336.1	80.8
0°-60°	396.9	95.4
0°-90°	416.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	416.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	469	
5°	455	42
15°	357	99
25°	242	110
35°	134	84
45°	54	43
55°	18	18
65°	11	11
75°	6	6
85°	2	2
90°	0	



TEST NUMBER: P1292102
CATALOG NUMBER: P3AS09R20W2N902765DE010 E3DLD1LI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	469.3
1°	469.8
2°	467.7
3°	465.0
4°	460.8
5°	455.0
6°	448.1
7°	440.7
8°	432.8
9°	423.3
10°	413.8
12.5°	386.3
15°	357.2
17.5°	327.6
20°	298.0
22.5°	268.4
25°	241.5
27.5°	214.5
30°	186.5
32.5°	160.1
35°	134.2
37.5°	111.5
40°	89.3
42.5°	70.3
45°	54.4
47.5°	41.2
50°	30.6
52.5°	22.7
55°	18.0
57.5°	16.4
60°	14.3
62.5°	12.7
65°	11.1
67.5°	9.5
70°	8.5
72.5°	6.9
75°	5.8
77.5°	4.8
80°	3.7
82.5°	2.6
85°	1.6
87.5°	0.5
90°	0.0

(END OF REPORT)