

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1292843

Luminaire Tested: P3AS09R30W2N902765DE010 E3PHLD1MW_3000K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1292843
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-12)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R30W2N902765DE010 E3PHLD1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R30 optic, 3000K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 453.0 lumens
Efficiency: N/A
Efficacy: 50.3 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1292843
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3PHLD1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1292843

CATALOG NUMBER: P3AS09R30W2N902765DE010 E3PHLD1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	43.9	9.7
10°-20°	93.7	20.7
20°-30°	96.0	21.2
30°-40°	78.5	17.3
40°-50°	58.7	13.0
50°-60°	41.3	9.1
60°-70°	25.9	5.7
70°-80°	12.5	2.8
80°-90°	2.4	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.7	51.6
0°-40°	312.2	68.9
0°-60°	412.2	91.0
0°-90°	453.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	453.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	509	
5°	485	44
15°	336	94
25°	208	96
35°	124	78
45°	76	59
55°	45	41
65°	26	26
75°	12	13
85°	2	2
90°	0	



TEST NUMBER: P1292843
CATALOG NUMBER: P3AS09R30W2N902765DE010 E3PHLD1MW_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	509.1
2.5°	504.0
5°	484.7
7.5°	452.8
10°	413.3
12.5°	374.7
15°	336.0
17.5°	300.7
20°	268.0
22.5°	236.9
25°	208.3
27.5°	183.1
30°	160.4
32.5°	142.0
35°	124.3
37.5°	110.0
40°	96.6
42.5°	85.7
45°	75.6
47.5°	66.4
50°	58.8
52.5°	52.1
55°	45.4
57.5°	40.3
60°	35.3
62.5°	30.2
65°	26.0
67.5°	21.8
70°	18.5
72.5°	15.1
75°	11.8
77.5°	8.4
80°	5.9
82.5°	3.4
85°	1.7
87.5°	0.8
90°	0.0

(END OF REPORT)