

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293441

Luminaire Tested: P3AS09R40W2N902765DE010 E3DLD1WMH\_3500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1293441  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R40W2N902765DE010 E3DLD1WMH\_3500K  
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3500K CCT AND, 90CRI ,  
E3DLD1WMH TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 529.0 lumens  
Efficiency: N/A  
Efficacy: 58.8 lumens/watt  
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1293441  
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLD1WMH\_3500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1293441

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLD1WMH\_3500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	49.4	9.3
10°-20°	122.5	23.2
20°-30°	141.6	26.8
30°-40°	111.6	21.1
40°-50°	57.3	10.8
50°-60°	21.9	4.1
60°-70°	14.5	2.7
70°-80°	7.9	1.5
80°-90°	2.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	313.5	59.3
0°-40°	425.1	80.4
0°-60°	504.3	95.3
0°-90°	529.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	529.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	542	
5°	530	49
15°	440	122
25°	310	142
35°	179	112
45°	74	57
55°	23	22
65°	15	14
75°	8	8
85°	2	2
90°	0	



TEST NUMBER: P1293441  
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLD1WMH\_3500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	541.5
2.5°	538.6
5°	529.7
7.5°	514.3
10°	493.6
12.5°	469.3
15°	439.7
17.5°	409.0
20°	375.8
22.5°	342.1
25°	309.5
27.5°	277.0
30°	245.0
32.5°	212.5
35°	178.7
37.5°	147.4
40°	119.0
42.5°	94.7
45°	74.0
47.5°	53.9
50°	36.7
52.5°	26.6
55°	23.1
57.5°	20.7
60°	18.9
62.5°	16.6
65°	14.8
67.5°	12.4
70°	10.7
72.5°	8.9
75°	7.7
77.5°	5.9
80°	4.1
82.5°	3.6
85°	1.8
87.5°	1.2
90°	0.0

(END OF REPORT)