

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293464

Luminaire Tested: P3AS09R40W2N902765DE010 E3DLP1MW_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293464
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R40W2N902765DE010 E3DLP1MW_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 3000K CCT AND, 90CRI ,
E3DLP1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 428.0 lumens
Efficiency: N/A
Efficacy: 47.6 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293464
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLP1MW_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293464

CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLP1MW_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.1	12.9
10°-20°	128.6	30.0
20°-30°	121.1	28.3
30°-40°	70.0	16.4
40°-50°	27.9	6.5
50°-60°	12.4	2.9
60°-70°	7.6	1.8
70°-80°	4.0	0.9
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	304.8	71.2
0°-40°	374.8	87.6
0°-60°	415.1	97.0
0°-90°	428.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	428.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	608	
5°	593	55
15°	467	129
25°	264	121
35°	110	70
45°	34	28
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1293464
CATALOG NUMBER: P3AS09R40W2N902765DE010 E3DLP1MW_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	607.8
2.5°	604.3
5°	593.2
7.5°	572.8
10°	546.0
12.5°	509.9
15°	466.7
17.5°	418.4
20°	365.9
22.5°	313.5
25°	264.5
27.5°	219.1
30°	177.7
32.5°	141.6
35°	110.1
37.5°	83.3
40°	62.3
42.5°	46.6
45°	34.4
47.5°	25.1
50°	18.6
52.5°	15.2
55°	13.4
57.5°	12.2
60°	10.5
62.5°	8.7
65°	7.6
67.5°	6.4
70°	5.8
72.5°	4.7
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)