

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293534

Luminaire Tested: P3AS09R45W2N902750DE010 E3DL1MW_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293534
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45W2N902750DE010 E3DL1MW_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 4000K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 661.0 lumens
Efficiency: N/A
Efficacy: 73.4 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293534
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1MW_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293534

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1MW_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.9	15.4
10°-20°	228.4	34.6
20°-30°	193.9	29.3
30°-40°	92.5	14.0
40°-50°	27.9	4.2
50°-60°	7.1	1.1
60°-70°	5.2	0.8
70°-80°	3.1	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	524.3	79.3
0°-40°	616.8	93.3
0°-60°	651.7	98.6
0°-90°	661.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	661.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1132	
5°	1101	102
15°	832	228
25°	423	194
35°	142	93
45°	34	28
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1293534
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1MW_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	1132.0
2.5°	1124.9
5°	1101.3
7.5°	1060.5
10°	1000.8
12.5°	921.6
15°	831.7
17.5°	731.8
20°	627.8
22.5°	522.0
25°	423.2
27.5°	333.4
30°	254.8
32.5°	191.5
35°	141.9
37.5°	104.6
40°	75.1
42.5°	52.0
45°	33.7
47.5°	18.9
50°	10.6
52.5°	8.3
55°	7.7
57.5°	7.1
60°	6.5
62.5°	5.9
65°	5.3
67.5°	4.7
70°	4.1
72.5°	3.5
75°	3.0
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)