

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293537

Luminaire Tested: P3AS09R45W2N902750DE010 E3DL1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293537
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45W2N902750DE010 E3DL1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3000K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 420.0 lumens
Efficiency: N/A
Efficacy: 46.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293537
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1293537

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.4	12.2
10°-20°	119.4	28.4
20°-30°	118.6	28.2
30°-40°	76.4	18.2
40°-50°	29.4	7.0
50°-60°	12.0	2.8
60°-70°	7.5	1.8
70°-80°	4.1	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	289.4	68.9
0°-40°	365.8	87.1
0°-60°	407.1	96.9
0°-90°	420.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	420.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	570	
5°	555	51
15°	432	119
25°	259	119
35°	122	76
45°	36	29
55°	13	12
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1293537
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1WH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	570.5
2.5°	567.6
5°	555.4
7.5°	534.4
10°	506.5
12.5°	471.5
15°	432.0
17.5°	388.9
20°	345.2
22.5°	301.0
25°	259.1
27.5°	219.5
30°	182.8
32.5°	150.8
35°	121.7
37.5°	95.5
40°	71.0
42.5°	51.2
45°	35.5
47.5°	23.9
50°	17.5
52.5°	14.6
55°	13.4
57.5°	11.6
60°	10.5
62.5°	8.7
65°	7.6
67.5°	6.4
70°	5.2
72.5°	4.7
75°	4.1
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)