

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293538

Luminaire Tested: P3AS09R45W2N902750DE010 E3DL1WH_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293538
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45W2N902750DE010 E3DL1WH_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 3500K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 427.0 lumens
Efficiency: N/A
Efficacy: 47.4 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293538
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1WH_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1293538

CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1WH_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.3	12.2
10°-20°	121.4	28.4
20°-30°	120.5	28.2
30°-40°	77.6	18.2
40°-50°	29.9	7.0
50°-60°	12.2	2.8
60°-70°	7.7	1.8
70°-80°	4.1	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	294.2	68.9
0°-40°	371.9	87.1
0°-60°	413.9	96.9
0°-90°	427.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	427.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	580	
5°	565	52
15°	439	121
25°	263	121
35°	124	78
45°	36	30
55°	14	12
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1293538
CATALOG NUMBER: P3AS09R45W2N902750DE010 E3DL1WH_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	580.0
2.5°	577.1
5°	564.6
7.5°	543.3
10°	514.9
12.5°	479.4
15°	439.2
17.5°	395.4
20°	351.0
22.5°	306.0
25°	263.4
27.5°	223.1
30°	185.8
32.5°	153.3
35°	123.7
37.5°	97.1
40°	72.2
42.5°	52.1
45°	36.1
47.5°	24.3
50°	17.8
52.5°	14.8
55°	13.6
57.5°	11.8
60°	10.7
62.5°	8.9
65°	7.7
67.5°	6.5
70°	5.3
72.5°	4.7
75°	4.1
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)