

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1293749

Luminaire Tested: P3AS09R45W2N902765DE010 E3DLP1WH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1293749
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-27)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R45W2N902765DE010 E3DLP1WH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 6500K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 658.0 lumens
Efficiency: N/A
Efficacy: 73.1 lumens/watt
Spacing Criteria (0/90/45): 0.69 / 0.69 / 0.69
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1293749
CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLP1WH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1293749

CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLP1WH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.5	15.4
10°-20°	227.4	34.6
20°-30°	193.1	29.3
30°-40°	92.1	14.0
40°-50°	27.7	4.2
50°-60°	7.0	1.1
60°-70°	5.2	0.8
70°-80°	3.1	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	521.9	79.3
0°-40°	614.0	93.3
0°-60°	648.8	98.6
0°-90°	658.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	658.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1127	
5°	1096	101
15°	828	227
25°	421	193
35°	141	92
45°	34	28
55°	8	7
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1293749
CATALOG NUMBER: P3AS09R45W2N902765DE010 E3DLP1WH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1126.9
2.5°	1119.8
5°	1096.3
7.5°	1055.7
10°	996.2
12.5°	917.4
15°	827.9
17.5°	728.5
20°	624.9
22.5°	519.6
25°	421.3
27.5°	331.9
30°	253.6
32.5°	190.7
35°	141.2
37.5°	104.2
40°	74.7
42.5°	51.8
45°	33.5
47.5°	18.8
50°	10.6
52.5°	8.2
55°	7.6
57.5°	7.1
60°	6.5
62.5°	5.9
65°	5.3
67.5°	4.7
70°	4.1
72.5°	3.5
75°	2.9
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)