

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294069

Luminaire Tested: P3AS09R50W2N902765DE010 E3DLP1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294069
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R50W2N902765DE010 E3DLP1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 2700K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 390.0 lumens
Efficiency: N/A
Efficacy: 43.3 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294069
CATALOG NUMBER: P3AS09R50W2N902765DE010 E3DLP1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1294069

CATALOG NUMBER: P3AS09R50W2N902765DE010 E3DLP1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	46.5	11.9
10°-20°	109.2	28.0
20°-30°	111.7	28.6
30°-40°	70.8	18.2
40°-50°	28.2	7.2
50°-60°	11.4	2.9
60°-70°	7.3	1.9
70°-80°	3.7	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	267.3	68.6
0°-40°	338.2	86.7
0°-60°	377.8	96.9
0°-90°	390.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	390.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	517	
5°	501	46
15°	394	109
25°	245	112
35°	112	71
45°	34	28
55°	13	11
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294069
CATALOG NUMBER: P3AS09R50W2N902765DE010 E3DLP1WMH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	517.3
2.5°	513.6
5°	501.4
7.5°	482.4
10°	457.1
12.5°	427.0
15°	394.3
17.5°	358.4
20°	320.9
22.5°	283.5
25°	245.4
27.5°	207.4
30°	172.1
32.5°	140.4
35°	111.9
37.5°	87.6
40°	66.5
42.5°	49.1
45°	34.3
47.5°	23.2
50°	16.9
52.5°	14.3
55°	12.7
57.5°	11.1
60°	9.5
62.5°	8.4
65°	7.4
67.5°	6.3
70°	5.3
72.5°	4.2
75°	3.7
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)