

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294213

Luminaire Tested: P3AS09R55W2N902750DE010 E3DLP1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294213
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55W2N902750DE010 E3DLP1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 645.0 lumens
Efficiency: N/A
Efficacy: 71.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294213
CATALOG NUMBER: P3AS09R55W2N902750DE010 E3DLP1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294213
 CATALOG NUMBER: P3AS09R55W2N902750DE010 E3DLP1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	74.9	11.6
10°-20°	190.6	29.6
20°-30°	199.8	31.0
30°-40°	116.5	18.1
40°-50°	43.6	6.8
50°-60°	10.3	1.6
60°-70°	5.2	0.8
70°-80°	3.2	0.5
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	465.3	72.1
0°-40°	581.8	90.2
0°-60°	635.7	98.6
0°-90°	645.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	645.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	808	
5°	796	75
15°	689	191
25°	441	200
35°	182	117
45°	53	44
55°	8	10
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1294213
CATALOG NUMBER: P3AS09R55W2N902750DE010 E3DLP1WH_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	807.7
2.5°	805.3
5°	796.5
7.5°	782.3
10°	760.4
12.5°	729.6
15°	689.4
17.5°	638.5
20°	578.7
22.5°	511.8
25°	440.8
27.5°	368.0
30°	298.8
32.5°	236.1
35°	182.2
37.5°	138.5
40°	102.4
42.5°	73.4
45°	53.3
47.5°	38.5
50°	26.0
52.5°	14.8
55°	8.3
57.5°	7.1
60°	6.5
62.5°	5.9
65°	5.3
67.5°	4.7
70°	4.1
72.5°	3.6
75°	3.0
77.5°	2.4
80°	1.8
82.5°	1.2
85°	0.6
87.5°	0.6
90°	0.0

(END OF REPORT)