

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294313

Luminaire Tested: P3AS09R55W2N902765DE010 E3DL1WH_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294313
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55W2N902765DE010 E3DL1WH_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 4000K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 430.0 lumens
Efficiency: N/A
Efficacy: 47.8 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294313
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DL1WH_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294313

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DL1WH_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.1	11.2
10°-20°	115.3	26.8
20°-30°	122.1	28.4
30°-40°	82.5	19.2
40°-50°	36.2	8.4
50°-60°	12.9	3.0
60°-70°	7.6	1.8
70°-80°	4.0	0.9
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	285.5	66.4
0°-40°	368.0	85.6
0°-60°	417.1	97.0
0°-90°	430.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	430.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	533	
5°	518	48
15°	416	115
25°	268	122
35°	131	83
45°	44	36
55°	13	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294313
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DL1WH_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	533.4
2.5°	529.3
5°	518.1
7.5°	499.8
10°	476.1
12.5°	447.8
15°	415.9
17.5°	380.4
20°	343.8
22.5°	305.4
25°	267.6
27.5°	230.4
30°	194.9
32.5°	161.3
35°	131.1
37.5°	104.0
40°	80.9
42.5°	60.8
45°	44.3
47.5°	32.5
50°	23.6
52.5°	16.5
55°	13.0
57.5°	11.8
60°	10.0
62.5°	8.9
65°	7.7
67.5°	6.5
70°	5.3
72.5°	4.7
75°	3.5
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)