

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294362

Luminaire Tested: P3AS09R55W2N902765DE010 E3DLP1GPH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294362
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R55W2N902765DE010 E3DLP1GPH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 5000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 210.0 lumens
Efficiency: N/A
Efficacy: 23.3 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294362
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLP1GPH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294362

CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLP1GPH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	23.5	11.2
10°-20°	56.3	26.8
20°-30°	59.6	28.4
30°-40°	40.3	19.2
40°-50°	17.7	8.4
50°-60°	6.3	3.0
60°-70°	3.7	1.8
70°-80°	1.9	0.9
80°-90°	0.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	139.4	66.4
0°-40°	179.7	85.6
0°-60°	203.7	97.0
0°-90°	210.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	210.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	260	
5°	253	23
15°	203	56
25°	131	60
35°	64	40
45°	22	18
55°	6	6
65°	4	4
75°	2	2
85°	1	1
90°	0	



TEST NUMBER: P1294362
CATALOG NUMBER: P3AS09R55W2N902765DE010 E3DLP1GPH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	260.5
2.5°	258.5
5°	253.0
7.5°	244.1
10°	232.5
12.5°	218.7
15°	203.1
17.5°	185.8
20°	167.9
22.5°	149.2
25°	130.7
27.5°	112.5
30°	95.2
32.5°	78.8
35°	64.0
37.5°	50.8
40°	39.5
42.5°	29.7
45°	21.6
47.5°	15.9
50°	11.5
52.5°	8.1
55°	6.3
57.5°	5.8
60°	4.9
62.5°	4.3
65°	3.8
67.5°	3.2
70°	2.6
72.5°	2.3
75°	1.7
77.5°	1.4
80°	1.2
82.5°	0.9
85°	0.6
87.5°	0.3
90°	0.0

(END OF REPORT)