

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294395

Luminaire Tested: P3AS09R60W2N902750DE010 E3CB1MB_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294395
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60W2N902750DE010 E3CB1MB_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3CB1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 754.0 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294395
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3CB1MB_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294395

CATALOG NUMBER: P3AS09R60W2N902750DE010 E3CB1MB_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	75.6	10.0
10°-20°	217.5	28.8
20°-30°	253.7	33.6
30°-40°	163.7	21.7
40°-50°	36.7	4.9
50°-60°	3.6	0.5
60°-70°	1.7	0.2
70°-80°	1.0	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	546.8	72.5
0°-40°	710.5	94.2
0°-60°	750.8	99.6
0°-90°	754.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	754.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	821	
5°	786	76
15°	794	218
25°	555	254
35°	265	164
45°	40	37
55°	3	4
65°	2	2
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P1294395
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3CB1MB_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	821.1
2.5°	807.7
5°	785.5
7.5°	784.4
10°	799.5
12.5°	809.4
15°	794.3
17.5°	748.8
20°	682.3
22.5°	612.9
25°	554.6
27.5°	497.4
30°	429.8
32.5°	350.5
35°	264.8
37.5°	180.8
40°	113.7
42.5°	68.2
45°	40.2
47.5°	23.3
50°	12.2
52.5°	4.1
55°	2.9
57.5°	2.3
60°	2.3
62.5°	1.7
65°	1.7
67.5°	1.7
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)