

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294529

Luminaire Tested: P3AS09R60W2N902750DE010 E3DLP1WH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294529
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60W2N902750DE010 E3DLP1WH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 556.0 lumens
Efficiency: N/A
Efficacy: 61.8 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294529
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLP1WH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1294529

CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLP1WH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	55.6	10.0
10°-20°	144.6	26.0
20°-30°	164.8	29.6
30°-40°	116.8	21.0
40°-50°	53.0	9.5
50°-60°	11.3	2.0
60°-70°	5.4	1.0
70°-80°	3.3	0.6
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	365.0	65.6
0°-40°	481.8	86.7
0°-60°	546.1	98.2
0°-90°	556.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	556.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	599	
5°	591	56
15°	521	145
25°	362	165
35°	186	117
45°	67	53
55°	8	11
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1294529
CATALOG NUMBER: P3AS09R60W2N902750DE010 E3DLP1WH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	598.7
2.5°	596.6
5°	590.8
7.5°	580.8
10°	567.0
12.5°	547.5
15°	521.0
17.5°	487.8
20°	448.7
22.5°	406.4
25°	362.0
27.5°	316.5
30°	271.1
32.5°	227.8
35°	186.0
37.5°	149.0
40°	115.7
42.5°	87.7
45°	66.6
47.5°	49.7
50°	32.8
52.5°	15.3
55°	8.5
57.5°	7.4
60°	6.9
62.5°	6.3
65°	5.3
67.5°	4.8
70°	4.2
72.5°	3.7
75°	3.2
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)