

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294557

Luminaire Tested: P3AS09R60W2N902765DE010 E3CD1MB_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294557
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60W2N902765DE010 E3CD1MB_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI , E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 683.0 lumens
Efficiency: N/A
Efficacy: 75.9 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294557
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3CD1MB_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1294557

CATALOG NUMBER: P3AS09R60W2N902765DE010 E3CD1MB_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	68.5	10.0
10°-20°	197.0	28.8
20°-30°	229.8	33.6
30°-40°	148.3	21.7
40°-50°	33.2	4.9
50°-60°	3.3	0.5
60°-70°	1.6	0.2
70°-80°	0.9	0.1
80°-90°	0.3	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	495.3	72.5
0°-40°	643.6	94.2
0°-60°	680.1	99.6
0°-90°	683.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	683.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	744	
5°	712	68
15°	720	197
25°	502	230
35°	240	148
45°	36	33
55°	3	3
65°	2	2
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P1294557
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3CD1MB_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	743.8
2.5°	731.6
5°	711.6
7.5°	710.5
10°	724.2
12.5°	733.2
15°	719.5
17.5°	678.3
20°	618.1
22.5°	555.2
25°	502.4
27.5°	450.6
30°	389.3
32.5°	317.5
35°	239.8
37.5°	163.8
40°	103.0
42.5°	61.8
45°	36.4
47.5°	21.1
50°	11.1
52.5°	3.7
55°	2.6
57.5°	2.1
60°	2.1
62.5°	1.6
65°	1.6
67.5°	1.6
70°	1.1
72.5°	1.1
75°	1.1
77.5°	0.5
80°	0.5
82.5°	0.5
85°	0.5
87.5°	0.0
90°	0.0

(END OF REPORT)