

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294561

Luminaire Tested: P3AS09R60W2N902765DE010 E3CD1MB_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294561
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-40)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60W2N902765DE010 E3CD1MB_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 5000K CCT AND, 90CRI ,
E3CD1MB TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 761.1 lumens
Efficiency: N/A
Efficacy: 84.6 lumens/watt
Spacing Criteria (0/90/45): 0.94 / 0.94 / 0.91
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294561
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3CD1MB_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294561

CATALOG NUMBER: P3AS09R60W2N902765DE010 E3CD1MB_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	76.3	10.0
10°-20°	219.5	28.8
20°-30°	256.1	33.6
30°-40°	165.2	21.7
40°-50°	37.0	4.9
50°-60°	3.7	0.5
60°-70°	1.8	0.2
70°-80°	1.0	0.1
80°-90°	0.4	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	551.9	72.5
0°-40°	717.1	94.2
0°-60°	757.8	99.6
0°-90°	761.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	761.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	829	
5°	793	76
15°	802	220
25°	560	256
35°	267	165
45°	41	37
55°	3	4
65°	2	2
75°	1	1
85°	1	0
90°	0	



TEST NUMBER: P1294561

CATALOG NUMBER: P3AS09R60W2N902765DE010 E3CD1MB_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	828.7
2.5°	815.2
5°	792.8
7.5°	791.6
10°	806.9
12.5°	816.9
15°	801.6
17.5°	755.7
20°	688.6
22.5°	618.6
25°	559.7
27.5°	502.1
30°	433.8
32.5°	353.7
35°	267.2
37.5°	182.5
40°	114.8
42.5°	68.9
45°	40.6
47.5°	23.5
50°	12.4
52.5°	4.1
55°	2.9
57.5°	2.4
60°	2.4
62.5°	1.8
65°	1.8
67.5°	1.8
70°	1.2
72.5°	1.2
75°	1.2
77.5°	0.6
80°	0.6
82.5°	0.6
85°	0.6
87.5°	0.0
90°	0.0

(END OF REPORT)