

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294690

Luminaire Tested: P3AS09R60W2N902765DE010 E3DLP1LI\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294690  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R60W2N902765DE010 E3DLP1LI\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,  
E3DLP1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 424.0 lumens  
Efficiency: N/A  
Efficacy: 47.1 lumens/watt  
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294690  
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DLP1LI\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1294690

CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DLP1LI\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	44.4	10.5
10°-20°	107.9	25.5
20°-30°	118.4	27.9
30°-40°	86.3	20.3
40°-50°	40.8	9.6
50°-60°	13.4	3.1
60°-70°	7.5	1.8
70°-80°	4.1	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	270.8	63.9
0°-40°	357.0	84.2
0°-60°	411.1	97.0
0°-90°	424.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	424.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	490	
5°	477	44
15°	389	108
25°	259	118
35°	138	86
45°	51	41
55°	13	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294690  
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DLP1LI\_3000K

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	490.0
2.5°	487.1
5°	477.2
7.5°	462.1
10°	441.7
12.5°	417.2
15°	388.6
17.5°	357.8
20°	325.1
22.5°	291.9
25°	259.3
27.5°	226.7
30°	195.8
32.5°	166.1
35°	137.5
37.5°	111.9
40°	88.6
42.5°	68.2
45°	51.3
47.5°	37.3
50°	25.6
52.5°	16.9
55°	13.4
57.5°	11.7
60°	10.5
62.5°	8.7
65°	7.6
67.5°	6.4
70°	5.2
72.5°	4.7
75°	4.1
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)