

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294702

Luminaire Tested: P3AS09R60W2N902765DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294702
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R60W2N902765DE010 E3DLP1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 613.0 lumens
Efficiency: N/A
Efficacy: 68.1 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294702
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294702
 CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DLP1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.3	10.0
10°-20°	159.4	26.0
20°-30°	181.7	29.6
30°-40°	128.8	21.0
40°-50°	58.5	9.5
50°-60°	12.4	2.0
60°-70°	6.0	1.0
70°-80°	3.7	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	402.4	65.6
0°-40°	531.2	86.7
0°-60°	602.1	98.2
0°-90°	613.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	613.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	660	
5°	651	61
15°	574	159
25°	399	182
35°	205	129
45°	73	58
55°	9	12
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294702
CATALOG NUMBER: P3AS09R60W2N902765DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	660.1
2.5°	657.8
5°	651.4
7.5°	640.3
10°	625.2
12.5°	603.6
15°	574.5
17.5°	537.8
20°	494.6
22.5°	448.0
25°	399.1
27.5°	349.0
30°	298.9
32.5°	251.1
35°	205.1
37.5°	164.3
40°	127.6
42.5°	96.7
45°	73.4
47.5°	54.8
50°	36.1
52.5°	16.9
55°	9.3
57.5°	8.2
60°	7.6
62.5°	7.0
65°	5.8
67.5°	5.2
70°	4.7
72.5°	4.1
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)