

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294783

Luminaire Tested: P3AS09R65W2N902750DE010 E3DL1MW_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294783
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902750DE010 E3DL1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,
E3DL1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 530.0 lumens
Efficiency: N/A
Efficacy: 58.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294783
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1294783

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	52.7	9.9
10°-20°	136.4	25.7
20°-30°	159.5	30.1
30°-40°	111.4	21.0
40°-50°	49.0	9.3
50°-60°	10.9	2.1
60°-70°	5.6	1.0
70°-80°	3.3	0.6
80°-90°	1.2	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	348.6	65.8
0°-40°	460.0	86.8
0°-60°	519.9	98.1
0°-90°	530.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	530.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	570	
5°	561	53
15°	490	136
25°	351	159
35°	177	111
45°	62	49
55°	9	11
65°	6	6
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1294783
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	570.0
2.5°	567.9
5°	561.0
7.5°	549.4
10°	533.5
12.5°	514.0
15°	490.2
17.5°	461.2
20°	429.0
22.5°	392.5
25°	351.3
27.5°	308.0
30°	262.5
32.5°	218.7
35°	177.0
37.5°	140.5
40°	108.3
42.5°	81.9
45°	61.8
47.5°	45.4
50°	28.5
52.5°	14.8
55°	9.0
57.5°	7.9
60°	6.9
62.5°	6.3
65°	5.8
67.5°	4.8
70°	4.2
72.5°	3.7
75°	3.2
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)