

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294784

Luminaire Tested: P3AS09R65W2N902750DE010 E3DL1MW\_3000K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1294784  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS09R65W2N902750DE010 E3DL1MW\_3000K  
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3000K CCT AND, 90CRI ,  
E3DL1MW TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 585.0 lumens  
Efficiency: N/A  
Efficacy: 65.0 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 9  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1294784  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1MW\_3000K

### Luminous Intensity Polar Plot







TEST NUMBER: P1294784

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1MW\_3000K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	58.1	9.9
10°-20°	150.6	25.7
20°-30°	176.0	30.1
30°-40°	123.0	21.0
40°-50°	54.1	9.3
50°-60°	12.0	2.1
60°-70°	6.1	1.0
70°-80°	3.7	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	384.7	65.8
0°-40°	507.7	86.8
0°-60°	573.9	98.1
0°-90°	585.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	585.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	629	
5°	619	58
15°	541	151
25°	388	176
35°	195	123
45°	68	54
55°	10	12
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294784  
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DL1MW\_3000K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	629.1
2.5°	626.8
5°	619.2
7.5°	606.4
10°	588.9
12.5°	567.3
15°	541.1
17.5°	509.0
20°	473.5
22.5°	433.2
25°	387.8
27.5°	339.9
30°	289.8
32.5°	241.4
35°	195.3
37.5°	155.1
40°	119.5
42.5°	90.4
45°	68.2
47.5°	50.1
50°	31.5
52.5°	16.3
55°	9.9
57.5°	8.7
60°	7.6
62.5°	7.0
65°	6.4
67.5°	5.2
70°	4.7
72.5°	4.1
75°	3.5
77.5°	2.9
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)