

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294838

Luminaire Tested: P3AS09R65W2N902750DE010 E3DLP1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294838
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902750DE010 E3DLP1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 2700K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 366.0 lumens
Efficiency: N/A
Efficacy: 40.7 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294838
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1294838

CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	10.5
10°-20°	92.7	25.3
20°-30°	102.5	28.0
30°-40°	74.4	20.3
40°-50°	34.9	9.5
50°-60°	11.7	3.2
60°-70°	6.8	1.9
70°-80°	3.5	1.0
80°-90°	1.2	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	233.5	63.8
0°-40°	307.9	84.1
0°-60°	354.5	96.9
0°-90°	366.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	366.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	424	
5°	412	38
15°	334	93
25°	225	102
35°	119	74
45°	44	35
55°	12	12
65°	7	7
75°	3	4
85°	1	1
90°	0	



TEST NUMBER: P1294838
CATALOG NUMBER: P3AS09R65W2N902750DE010 E3DLP1LI_2700K

CANDELA DISTRIBUTION (FULL):

0°	
0°	424.3
2.5°	421.6
5°	412.1
7.5°	397.9
10°	379.4
12.5°	357.8
15°	333.5
17.5°	307.1
20°	280.2
22.5°	252.2
25°	224.8
27.5°	196.8
30°	169.4
32.5°	143.0
35°	118.7
37.5°	96.6
40°	76.5
42.5°	58.6
45°	43.8
47.5°	31.7
50°	21.6
52.5°	14.8
55°	12.1
57.5°	10.6
60°	9.0
62.5°	7.9
65°	6.9
67.5°	5.8
70°	4.7
72.5°	4.2
75°	3.2
77.5°	2.6
80°	2.1
82.5°	1.6
85°	1.1
87.5°	0.5
90°	0.0

(END OF REPORT)