

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294935

Luminaire Tested: P3AS09R65W2N902765DE010 E3DL1H_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294935
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902765DE010 E3DL1H_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 6500K CCT AND, 90CRI ,
E3DL1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 590.0 lumens
Efficiency: N/A
Efficacy: 65.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294935
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DL1H_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1294935

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DL1H_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.6	9.9
10°-20°	151.9	25.7
20°-30°	177.5	30.1
30°-40°	124.1	21.0
40°-50°	54.6	9.3
50°-60°	12.2	2.1
60°-70°	6.2	1.1
70°-80°	3.7	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	388.0	65.8
0°-40°	512.1	86.8
0°-60°	578.8	98.1
0°-90°	590.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	590.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	634	
5°	624	59
15°	546	152
25°	391	177
35°	197	124
45°	69	55
55°	10	12
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294935
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DL1H_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	634.5
2.5°	632.2
5°	624.5
7.5°	611.6
10°	593.9
12.5°	572.2
15°	545.7
17.5°	513.4
20°	477.5
22.5°	436.9
25°	391.1
27.5°	342.8
30°	292.3
32.5°	243.5
35°	197.0
37.5°	156.4
40°	120.6
42.5°	91.2
45°	68.8
47.5°	50.6
50°	31.8
52.5°	16.5
55°	10.0
57.5°	8.8
60°	7.6
62.5°	7.1
65°	6.5
67.5°	5.3
70°	4.7
72.5°	4.1
75°	3.5
77.5°	2.9
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)