

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1294939

Luminaire Tested: P3AS09R65W2N902765DE010 E3DL1LI_4000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1294939
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-43)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R65W2N902765DE010 E3DL1LI_4000K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 4000K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 593.0 lumens
Efficiency: N/A
Efficacy: 65.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1294939
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DL1LI_4000K

Luminous Intensity Polar Plot





TEST NUMBER: P1294939

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DL1LI_4000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	58.9	9.9
10°-20°	152.7	25.7
20°-30°	178.4	30.1
30°-40°	124.7	21.0
40°-50°	54.9	9.3
50°-60°	12.2	2.1
60°-70°	6.2	1.0
70°-80°	3.7	0.6
80°-90°	1.3	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	390.0	65.8
0°-40°	514.7	86.8
0°-60°	581.8	98.1
0°-90°	593.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	593.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	638	
5°	628	59
15°	548	153
25°	393	178
35°	198	125
45°	69	55
55°	10	12
65°	6	6
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1294939
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DL1LI_4000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	637.8
2.5°	635.4
5°	627.7
7.5°	614.7
10°	597.0
12.5°	575.1
15°	548.5
17.5°	516.0
20°	479.9
22.5°	439.2
25°	393.1
27.5°	344.6
30°	293.8
32.5°	244.7
35°	198.0
37.5°	157.2
40°	121.2
42.5°	91.6
45°	69.2
47.5°	50.8
50°	31.9
52.5°	16.5
55°	10.0
57.5°	8.9
60°	7.7
62.5°	7.1
65°	6.5
67.5°	5.3
70°	4.7
72.5°	4.1
75°	3.5
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)