

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295010

Luminaire Tested: P3AS09R65W2N902765DE010 E3DLP1LI_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-41)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRIS
Catalog Number: P3AS09R65W2N902765DE010 E3DLP1LI_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R65 optic, 3500K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 410.0 lumens
Efficiency: N/A
Efficacy: 45.6 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295010
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLP1LI_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1295010

CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLP1LI_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	42.9	10.5
10°-20°	103.8	25.3
20°-30°	114.8	28.0
30°-40°	83.4	20.3
40°-50°	39.1	9.5
50°-60°	13.1	3.2
60°-70°	7.6	1.9
70°-80°	4.0	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	261.5	63.8
0°-40°	344.9	84.1
0°-60°	397.1	96.9
0°-90°	410.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	410.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	475	
5°	462	43
15°	374	104
25°	252	115
35°	133	83
45°	49	39
55°	14	13
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1295010
CATALOG NUMBER: P3AS09R65W2N902765DE010 E3DLP1LI_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	475.3
2.5°	472.3
5°	461.7
7.5°	445.7
10°	425.0
12.5°	400.8
15°	373.6
17.5°	344.0
20°	313.9
22.5°	282.6
25°	251.8
27.5°	220.5
30°	189.7
32.5°	160.2
35°	133.0
37.5°	108.2
40°	85.7
42.5°	65.6
45°	49.1
47.5°	35.5
50°	24.2
52.5°	16.6
55°	13.6
57.5°	11.8
60°	10.0
62.5°	8.9
65°	7.7
67.5°	6.5
70°	5.3
72.5°	4.7
75°	3.5
77.5°	3.0
80°	2.4
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)