

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295141

Luminaire Tested: P3AS09R70W2N902750DE010 E3DLP1WH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295141
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-47)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902750DE010 E3DLP1WH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 5000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 592.0 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.97 / 0.97 / 0.98
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295141
CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DLP1WH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295141

CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DLP1WH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.4	8.2
10°-20°	129.8	21.9
20°-30°	168.7	28.5
30°-40°	143.2	24.2
40°-50°	73.8	12.5
50°-60°	14.2	2.4
60°-70°	7.7	1.3
70°-80°	4.7	0.8
80°-90°	1.4	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	347.0	58.6
0°-40°	490.2	82.8
0°-60°	578.2	97.7
0°-90°	592.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	592.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	523	
5°	514	48
15°	464	130
25°	370	169
35°	230	143
45°	95	74
55°	11	14
65°	8	8
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P1295141
CATALOG NUMBER: P3AS09R70W2N902750DE010 E3DLP1WH_5000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	522.6
2.5°	520.9
5°	514.4
7.5°	505.0
10°	493.8
12.5°	479.7
15°	463.9
17.5°	444.5
20°	422.7
22.5°	398.0
25°	370.4
27.5°	339.2
30°	305.7
32.5°	268.7
35°	230.5
37.5°	192.8
40°	157.0
42.5°	123.5
45°	95.2
47.5°	70.0
50°	40.6
52.5°	17.6
55°	11.2
57.5°	10.6
60°	9.4
62.5°	8.8
65°	7.6
67.5°	7.1
70°	5.9
72.5°	5.3
75°	4.7
77.5°	3.5
80°	2.9
82.5°	1.8
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)