

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295248

Luminaire Tested: P3AS09R70W2N902765DE010 E3DL1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295248
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-45)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS09R70W2N902765DE010 E3DL1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R70 optic, 3000K CCT AND, 90CRI ,
E3DL1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 419.0 lumens
Efficiency: N/A
Efficacy: 46.6 lumens/watt
Spacing Criteria (0/90/45): 0.82 / 0.82 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 9
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295248
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1295248

CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.9	9.8
10°-20°	101.2	24.2
20°-30°	115.2	27.5
30°-40°	90.1	21.5
40°-50°	44.3	10.6
50°-60°	13.6	3.2
60°-70°	8.1	1.9
70°-80°	4.3	1.0
80°-90°	1.3	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	257.4	61.4
0°-40°	347.5	82.9
0°-60°	405.3	96.7
0°-90°	419.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	419.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	448	
5°	438	41
15°	364	101
25°	252	115
35°	144	90
45°	56	44
55°	14	14
65°	8	8
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1295248
CATALOG NUMBER: P3AS09R70W2N902765DE010 E3DL1WH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	448.2
2.5°	445.9
5°	438.3
7.5°	426.0
10°	408.6
12.5°	388.2
15°	363.7
17.5°	337.5
20°	309.5
22.5°	280.3
25°	251.8
27.5°	223.8
30°	197.0
32.5°	170.2
35°	144.5
37.5°	120.1
40°	96.8
42.5°	75.2
45°	56.5
47.5°	39.6
50°	25.6
52.5°	16.9
55°	14.0
57.5°	12.2
60°	10.5
62.5°	9.3
65°	8.2
67.5°	7.0
70°	5.8
72.5°	4.7
75°	4.1
77.5°	3.5
80°	2.3
82.5°	1.7
85°	1.2
87.5°	0.6
90°	0.0

(END OF REPORT)