

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295914

Luminaire Tested: P3AS13R20W2N902765DE010 E3DLD1WH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295914
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-6)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20W2N902765DE010 E3DLD1WH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 6500K CCT AND, 90CRI ,
E3DLD1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 607.0 lumens
Efficiency: N/A
Efficacy: 49.3 lumens/watt
Spacing Criteria (0/90/45): 0.76 / 0.76 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295914
CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLD1WH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1295914

CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLD1WH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.4	10.1
10°-20°	145.1	23.9
20°-30°	161.1	26.5
30°-40°	122.9	20.2
40°-50°	62.9	10.4
50°-60°	25.8	4.3
60°-70°	16.1	2.7
70°-80°	9.0	1.5
80°-90°	2.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	367.6	60.6
0°-40°	490.5	80.8
0°-60°	579.2	95.4
0°-90°	607.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	607.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	685	
5°	664	61
15°	521	145
25°	352	161
35°	196	123
45°	79	63
55°	26	26
65°	16	16
75°	8	9
85°	2	3
90°	0	



TEST NUMBER: P1295914
CATALOG NUMBER: P3AS13R20W2N902765DE010 E3DLD1WH_6500K

CANDELA DISTRIBUTION (FULL):

0°	
0°	684.7
1°	685.5
2°	682.4
3°	678.5
4°	672.4
5°	663.9
6°	653.9
7°	643.1
8°	631.5
9°	617.6
10°	603.7
12.5°	563.6
15°	521.2
17.5°	478.1
20°	434.9
22.5°	391.7
25°	352.4
27.5°	313.1
30°	272.2
32.5°	233.6
35°	195.8
37.5°	162.7
40°	130.3
42.5°	102.6
45°	79.4
47.5°	60.1
50°	44.7
52.5°	33.2
55°	26.2
57.5°	23.9
60°	20.8
62.5°	18.5
65°	16.2
67.5°	13.9
70°	12.3
72.5°	10.0
75°	8.5
77.5°	6.9
80°	5.4
82.5°	3.9
85°	2.3
87.5°	0.8
90°	0.0

(END OF REPORT)