

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1295933

Luminaire Tested: P3AS13R20W2N902765DE010 E3PHLD1MW_2700K

Issue Date: 1/29/2026

Test Information

Test Method: LM-79-2019
Report Number: P1295933
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2509-551-10)
Test Lab: INNOVATION CENTER
Issue Date: 1/29/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R20W2N902765DE010 E3PHLD1MW_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R20 optic, 2700K CCT AND, 90CRI ,
E3PHLD1MW TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 477.0 lumens
Efficiency: N/A
Efficacy: 38.8 lumens/watt
Spacing Criteria (0/90/45): 0.58 / 0.58 / 0.68
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1295933
CATALOG NUMBER: P3AS13R20W2N902765DE010 E3PHLD1MW_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1295933

CATALOG NUMBER: P3AS13R20W2N902765DE010 E3PHLD1MW_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	51.5	10.8
10°-20°	102.7	21.5
20°-30°	99.8	20.9
30°-40°	80.6	16.9
40°-50°	59.9	12.6
50°-60°	41.6	8.7
60°-70°	26.1	5.5
70°-80°	12.6	2.7
80°-90°	2.2	0.5
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	254.0	53.3
0°-40°	334.6	70.1
0°-60°	436.2	91.4
0°-90°	477.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	477.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	617	
5°	571	52
15°	367	103
25°	216	100
35°	128	81
45°	77	60
55°	46	42
65°	26	26
75°	12	13
85°	2	2
90°	0	



TEST NUMBER: P1295933
CATALOG NUMBER: P3AS13R20W2N902765DE010 E3PHLD1MW_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	616.9
2.5°	602.9
5°	570.9
7.5°	527.9
10°	477.9
12.5°	422.9
15°	366.9
17.5°	321.0
20°	281.0
22.5°	246.0
25°	216.0
27.5°	190.0
30°	166.0
32.5°	146.0
35°	128.0
37.5°	112.0
40°	99.0
42.5°	87.0
45°	77.0
47.5°	68.0
50°	60.0
52.5°	53.0
55°	46.0
57.5°	40.0
60°	35.0
62.5°	31.0
65°	26.0
67.5°	22.0
70°	18.0
72.5°	15.0
75°	12.0
77.5°	9.0
80°	6.0
82.5°	3.0
85°	2.0
87.5°	0.0
90°	0.0

(END OF REPORT)