

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297101

Luminaire Tested: P3AS13R40W2N902750DE010 E3DLP1WMH_5000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297101
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-21)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40W2N902750DE010 E3DLP1WMH_5000K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 5000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 567.0 lumens
Efficiency: N/A
Efficacy: 46.1 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.74
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297101
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLP1WMH_5000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297101

CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLP1WMH_5000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	73.0	12.9
10°-20°	170.3	30.0
20°-30°	160.5	28.3
30°-40°	92.8	16.4
40°-50°	37.0	6.5
50°-60°	16.4	2.9
60°-70°	10.1	1.8
70°-80°	5.3	0.9
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	403.8	71.2
0°-40°	496.6	87.6
0°-60°	549.9	97.0
0°-90°	567.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	567.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	805	
5°	786	73
15°	618	170
25°	350	160
35°	146	93
45°	46	37
55°	18	16
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1297101
CATALOG NUMBER: P3AS13R40W2N902750DE010 E3DLP1WMH_5000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	805.1
2.5°	800.5
5°	785.8
7.5°	758.8
10°	723.3
12.5°	675.4
15°	618.3
17.5°	554.3
20°	484.8
22.5°	415.3
25°	350.5
27.5°	290.3
30°	235.4
32.5°	187.6
35°	145.9
37.5°	110.4
40°	82.6
42.5°	61.8
45°	45.5
47.5°	33.2
50°	24.7
52.5°	20.1
55°	17.8
57.5°	16.2
60°	13.9
62.5°	11.6
65°	10.0
67.5°	8.5
70°	7.7
72.5°	6.2
75°	4.6
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)