

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297173

Luminaire Tested: P3AS13R40W2N902765DE010 E3DL1GPH_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297173
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-23)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40W2N902765DE010 E3DL1GPH_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 6500K CCT AND, 90CRI ,
E3DL1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 440.0 lumens
Efficiency: N/A
Efficacy: 35.8 lumens/watt
Spacing Criteria (0/90/45): 0.65 / 0.65 / 0.63
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297173
CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DL1GPH_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1297173

CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DL1GPH_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.2	18.0
10°-20°	170.0	38.6
20°-30°	121.3	27.6
30°-40°	44.7	10.1
40°-50°	14.1	3.2
50°-60°	4.9	1.1
60°-70°	3.4	0.8
70°-80°	2.0	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	370.5	84.2
0°-40°	415.1	94.3
0°-60°	434.1	98.6
0°-90°	440.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	440.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	888	
5°	859	79
15°	624	170
25°	261	121
35°	66	45
45°	17	14
55°	5	5
65°	3	3
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P1297173
CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DL1GPH_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	887.9
2.5°	881.1
5°	858.8
7.5°	821.8
10°	770.4
12.5°	705.1
15°	624.3
17.5°	533.6
20°	438.1
22.5°	344.1
25°	261.3
27.5°	191.9
30°	135.2
32.5°	94.8
35°	66.1
37.5°	46.8
40°	33.6
42.5°	24.2
45°	17.4
47.5°	11.7
50°	7.9
52.5°	5.7
55°	5.3
57.5°	4.9
60°	4.2
62.5°	3.8
65°	3.4
67.5°	3.0
70°	2.6
72.5°	2.3
75°	1.9
77.5°	1.5
80°	1.1
82.5°	0.8
85°	0.4
87.5°	0.4
90°	0.0

(END OF REPORT)