

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297215

Luminaire Tested: P3AS13R40W2N902765DE010 E3DLD1H_6500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297215
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-22)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R40W2N902765DE010 E3DLD1H_6500K
Description: 3in Adjustable Tunable White LED luminaire with, R40 optic, 6500K CCT AND, 90CRI ,
E3DLD1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 689.0 lumens
Efficiency: N/A
Efficacy: 56.0 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.88
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297215
CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DLD1H_6500K

Luminous Intensity Polar Plot





TEST NUMBER: P1297215

CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DLD1H_6500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	64.3	9.3
10°-20°	159.5	23.2
20°-30°	184.5	26.8
30°-40°	145.3	21.1
40°-50°	74.6	10.8
50°-60°	28.5	4.1
60°-70°	18.9	2.7
70°-80°	10.3	1.5
80°-90°	3.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	408.3	59.3
0°-40°	553.7	80.4
0°-60°	656.8	95.3
0°-90°	689.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	689.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	705	
5°	690	64
15°	573	160
25°	403	184
35°	233	145
45°	96	75
55°	30	29
65°	19	19
75°	10	10
85°	2	3
90°	0	



TEST NUMBER: P1297215
CATALOG NUMBER: P3AS13R40W2N902765DE010 E3DLD1H_6500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	705.3
2.5°	701.5
5°	689.9
7.5°	669.9
10°	642.9
12.5°	611.3
15°	572.7
17.5°	532.7
20°	489.5
22.5°	445.6
25°	403.2
27.5°	360.8
30°	319.1
32.5°	276.7
35°	232.8
37.5°	191.9
40°	154.9
42.5°	123.3
45°	96.4
47.5°	70.1
50°	47.8
52.5°	34.7
55°	30.1
57.5°	27.0
60°	24.7
62.5°	21.6
65°	19.3
67.5°	16.2
70°	13.9
72.5°	11.6
75°	10.0
77.5°	7.7
80°	5.4
82.5°	4.6
85°	2.3
87.5°	1.5
90°	0.0

(END OF REPORT)