

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297527

Luminaire Tested: P3AS13R45W2N902765DE010 E3DLP1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-25)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R45W2N902765DE010 E3DLP1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R45 optic, 2700K CCT AND, 90CRI ,
E3DLP1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 500.0 lumens
Efficiency: N/A
Efficacy: 40.7 lumens/watt
Spacing Criteria (0/90/45): 0.73 / 0.73 / 0.76
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297527
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLP1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1297527

CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLP1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	61.2	12.2
10°-20°	142.2	28.4
20°-30°	141.1	28.2
30°-40°	90.9	18.2
40°-50°	35.0	7.0
50°-60°	14.2	2.8
60°-70°	9.0	1.8
70°-80°	4.9	1.0
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	344.5	68.9
0°-40°	435.4	87.1
0°-60°	484.7	96.9
0°-90°	500.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	500.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	679	
5°	661	61
15°	514	142
25°	308	141
35°	145	91
45°	42	35
55°	16	14
65°	9	9
75°	5	5
85°	1	2
90°	0	



TEST NUMBER: P1297527
CATALOG NUMBER: P3AS13R45W2N902765DE010 E3DLP1LI_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	679.2
2.5°	675.7
5°	661.2
7.5°	636.2
10°	602.9
12.5°	561.4
15°	514.2
17.5°	462.9
20°	411.0
22.5°	358.3
25°	308.4
27.5°	261.3
30°	217.6
32.5°	179.5
35°	144.8
37.5°	113.7
40°	84.6
42.5°	61.0
45°	42.3
47.5°	28.4
50°	20.8
52.5°	17.3
55°	15.9
57.5°	13.9
60°	12.5
62.5°	10.4
65°	9.0
67.5°	7.6
70°	6.2
72.5°	5.5
75°	4.9
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)