

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297865

Luminaire Tested: P3AS13R50W2N902765DE010 E3DLP1WMH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297865
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-29)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R50W2N902765DE010 E3DLP1WMH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R50 optic, 3000K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 564.0 lumens
Efficiency: N/A
Efficacy: 45.9 lumens/watt
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.77
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297865
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DLP1WMH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1297865

CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DLP1WMH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	67.2	11.9
10°-20°	157.9	28.0
20°-30°	161.5	28.6
30°-40°	102.4	18.2
40°-50°	40.8	7.2
50°-60°	16.5	2.9
60°-70°	10.6	1.9
70°-80°	5.4	1.0
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	386.6	68.6
0°-40°	489.0	86.7
0°-60°	546.3	96.9
0°-90°	564.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	748	
5°	725	67
15°	570	158
25°	355	162
35°	162	102
45°	50	41
55°	18	16
65°	11	11
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1297865
CATALOG NUMBER: P3AS13R50W2N902765DE010 E3DLP1WMH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	748.1
2.5°	742.7
5°	725.2
7.5°	697.7
10°	661.1
12.5°	617.5
15°	570.2
17.5°	518.3
20°	464.1
22.5°	409.9
25°	355.0
27.5°	300.0
30°	248.8
32.5°	203.0
35°	161.8
37.5°	126.7
40°	96.2
42.5°	71.0
45°	49.6
47.5°	33.6
50°	24.4
52.5°	20.6
55°	18.3
57.5°	16.0
60°	13.7
62.5°	12.2
65°	10.7
67.5°	9.2
70°	7.6
72.5°	6.1
75°	5.3
77.5°	3.8
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)