

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1297992

Luminaire Tested: P3AS13R55W2N902750DE010 E3DLP1H_3500K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1297992
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55W2N902750DE010 E3DLP1H_3500K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3500K CCT AND, 90CRI ,
E3DLP1H TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 564.0 lumens
Efficiency: N/A
Efficacy: 45.9 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1297992
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1H_3500K

Luminous Intensity Polar Plot





TEST NUMBER: P1297992

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1H_3500K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	63.1	11.2
10°-20°	151.2	26.8
20°-30°	160.2	28.4
30°-40°	108.2	19.2
40°-50°	47.4	8.4
50°-60°	17.0	3.0
60°-70°	10.0	1.8
70°-80°	5.2	0.9
80°-90°	1.7	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	374.5	66.4
0°-40°	482.7	85.6
0°-60°	547.1	97.0
0°-90°	564.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	700	
5°	680	63
15°	546	151
25°	351	160
35°	172	108
45°	58	47
55°	17	17
65°	10	10
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1297992
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1H_3500K

CANDELA DISTRIBUTION (FULL):

	0°
0°	699.7
2.5°	694.3
5°	679.5
7.5°	655.5
10°	624.5
12.5°	587.3
15°	545.5
17.5°	499.0
20°	451.0
22.5°	400.6
25°	351.0
27.5°	302.2
30°	255.7
32.5°	211.5
35°	172.0
37.5°	136.4
40°	106.2
42.5°	79.8
45°	58.1
47.5°	42.6
50°	31.0
52.5°	21.7
55°	17.0
57.5°	15.5
60°	13.2
62.5°	11.6
65°	10.1
67.5°	8.5
70°	7.0
72.5°	6.2
75°	4.6
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)