

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298006

Luminaire Tested: P3AS13R55W2N902750DE010 E3DLP1WH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298006
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-35)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55W2N902750DE010 E3DLP1WH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 3000K CCT AND, 90CRI ,
E3DLP1WH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 833.0 lumens
Efficiency: N/A
Efficacy: 67.7 lumens/watt
Spacing Criteria (0/90/45): 0.83 / 0.83 / 0.81
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298006
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1WH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298006

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1WH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	96.7	11.6
10°-20°	246.2	29.6
20°-30°	258.0	31.0
30°-40°	150.5	18.1
40°-50°	56.3	6.8
50°-60°	13.3	1.6
60°-70°	6.8	0.8
70°-80°	4.0	0.5
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	600.9	72.1
0°-40°	751.4	90.2
0°-60°	821.0	98.6
0°-90°	833.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	833.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1043	
5°	1029	97
15°	890	246
25°	569	258
35°	235	151
45°	69	56
55°	11	13
65°	7	7
75°	4	4
85°	1	1
90°	0	



TEST NUMBER: P1298006
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1WH_3000K

CANDELA DISTRIBUTION (FULL):

0°	
0°	1043.1
2.5°	1040.1
5°	1028.6
7.5°	1010.3
10°	982.0
12.5°	942.2
15°	890.3
17.5°	824.6
20°	747.4
22.5°	661.0
25°	569.3
27.5°	475.3
30°	385.9
32.5°	304.9
35°	235.4
37.5°	178.8
40°	132.2
42.5°	94.8
45°	68.8
47.5°	49.7
50°	33.6
52.5°	19.1
55°	10.7
57.5°	9.2
60°	8.4
62.5°	7.6
65°	6.9
67.5°	6.1
70°	5.3
72.5°	4.6
75°	3.8
77.5°	3.1
80°	2.3
82.5°	1.5
85°	0.8
87.5°	0.8
90°	0.0

(END OF REPORT)