

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298010

Luminaire Tested: P3AS13R55W2N902750DE010 E3DLP1WMH_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298010
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-33)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R55W2N902750DE010 E3DLP1WMH_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R55 optic, 2700K CCT AND, 90CRI ,
E3DLP1WMH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 504.0 lumens
Efficiency: N/A
Efficacy: 41.0 lumens/watt
Spacing Criteria (0/90/45): 0.77 / 0.77 / 0.8
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298010
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1WMH_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1298010

CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1WMH_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	56.4	11.2
10°-20°	135.1	26.8
20°-30°	143.1	28.4
30°-40°	96.7	19.2
40°-50°	42.4	8.4
50°-60°	15.2	3.0
60°-70°	8.9	1.8
70°-80°	4.7	0.9
80°-90°	1.5	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	334.7	66.4
0°-40°	431.4	85.6
0°-60°	488.9	97.0
0°-90°	504.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	504.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	625	
5°	607	56
15°	488	135
25°	314	143
35°	154	97
45°	52	42
55°	15	15
65°	9	9
75°	4	5
85°	1	2
90°	0	



TEST NUMBER: P1298010
CATALOG NUMBER: P3AS13R55W2N902750DE010 E3DLP1WMH_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	625.2
2.5°	620.4
5°	607.2
7.5°	585.8
10°	558.1
12.5°	524.8
15°	487.5
17.5°	445.9
20°	403.0
22.5°	358.0
25°	313.7
27.5°	270.0
30°	228.5
32.5°	189.0
35°	153.7
37.5°	121.9
40°	94.9
42.5°	71.3
45°	51.9
47.5°	38.1
50°	27.7
52.5°	19.4
55°	15.2
57.5°	13.8
60°	11.8
62.5°	10.4
65°	9.0
67.5°	7.6
70°	6.2
72.5°	5.5
75°	4.2
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)