

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298254

Luminaire Tested: P3AS13R60W2N902750DE010 E3DL1LI_2700K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298254
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60W2N902750DE010 E3DL1LI_2700K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 2700K CCT AND, 90CRI ,
E3DL1LI TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 729.0 lumens
Efficiency: N/A
Efficacy: 59.3 lumens/watt
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298254
CATALOG NUMBER: P3AS13R60W2N902750DE010 E3DL1LI_2700K

Luminous Intensity Polar Plot





TEST NUMBER: P1298254

CATALOG NUMBER: P3AS13R60W2N902750DE010 E3DL1LI_2700K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	72.9	10.0
10°-20°	189.5	26.0
20°-30°	216.0	29.6
30°-40°	153.2	21.0
40°-50°	69.5	9.5
50°-60°	14.8	2.0
60°-70°	7.1	1.0
70°-80°	4.4	0.6
80°-90°	1.5	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	478.5	65.6
0°-40°	631.7	86.7
0°-60°	716.0	98.2
0°-90°	729.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	729.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	785	
5°	775	73
15°	683	190
25°	475	216
35°	244	153
45°	87	70
55°	11	15
65°	7	7
75°	4	4
85°	1	2
90°	0	



TEST NUMBER: P1298254
CATALOG NUMBER: P3AS13R60W2N902750DE010 E3DL1LI_2700K

CANDELA DISTRIBUTION (FULL):

	0°
0°	785.0
2.5°	782.3
5°	774.6
7.5°	761.5
10°	743.5
12.5°	717.8
15°	683.2
17.5°	639.5
20°	588.2
22.5°	532.8
25°	474.6
27.5°	415.0
30°	355.4
32.5°	298.6
35°	243.9
37.5°	195.4
40°	151.7
42.5°	115.0
45°	87.3
47.5°	65.1
50°	43.0
52.5°	20.1
55°	11.1
57.5°	9.7
60°	9.0
62.5°	8.3
65°	6.9
67.5°	6.2
70°	5.5
72.5°	4.9
75°	4.2
77.5°	3.5
80°	2.8
82.5°	2.1
85°	1.4
87.5°	0.7
90°	0.0

(END OF REPORT)