

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298417

Luminaire Tested: P3AS13R60W2N902765DE010 E3DL1LI\_6500K

Issue Date: 1/30/2026

**Test Information**


Test Method: LM-79-2019  
Report Number: P1298417  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-39)  
Test Lab: INNOVATION CENTER  
Issue Date: 1/30/2026  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: IRiS  
Catalog Number: P3AS13R60W2N902765DE010 E3DL1LI\_6500K  
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 6500K CCT AND, 90CRI ,  
E3DL1LI TRIM  
Light Source: -  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 811.0 lumens  
Efficiency: N/A  
Efficacy: 65.9 lumens/watt  
Spacing Criteria (0/90/45): 0.87 / 0.87 / 0.87  
Luminous Opening: Circular (Dia: 0.25' x H: 0')  
CIE Type: Direct  
  
Input Watts (W): 12.3  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT

TEST NUMBER: P1298417  
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DL1LI\_6500K

### Luminous Intensity Polar Plot







TEST NUMBER: P1298417

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DL1LI\_6500K

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	81.1	10.0
10°-20°	210.9	26.0
20°-30°	240.3	29.6
30°-40°	170.4	21.0
40°-50°	77.3	9.5
50°-60°	16.4	2.0
60°-70°	7.9	1.0
70°-80°	4.9	0.6
80°-90°	1.7	0.2
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	532.4	65.6
0°-40°	702.8	86.7
0°-60°	796.5	98.2
0°-90°	811.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	811.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	873	
5°	862	81
15°	760	211
25°	528	240
35°	271	170
45°	97	77
55°	12	16
65°	8	8
75°	5	5
85°	2	2
90°	0	



TEST NUMBER: P1298417  
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DL1LI\_6500K

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	873.3
2.5°	870.2
5°	861.8
7.5°	847.1
10°	827.1
12.5°	798.6
15°	760.0
17.5°	711.5
20°	654.4
22.5°	592.8
25°	528.0
27.5°	461.7
30°	395.4
32.5°	332.2
35°	271.3
37.5°	217.4
40°	168.8
42.5°	128.0
45°	97.1
47.5°	72.5
50°	47.8
52.5°	22.4
55°	12.3
57.5°	10.8
60°	10.0
62.5°	9.2
65°	7.7
67.5°	6.9
70°	6.2
72.5°	5.4
75°	4.6
77.5°	3.9
80°	3.1
82.5°	2.3
85°	1.5
87.5°	0.8
90°	0.0

(END OF REPORT)