

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for
Cooper Lighting Solutions

Brand: IRiS

Report Number: P1298473

Luminaire Tested: P3AS13R60W2N902765DE010 E3DLP1GPH_3000K

Issue Date: 1/30/2026

Test Information

Test Method: LM-79-2019
Report Number: P1298473
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2601-647-37)
Test Lab: INNOVATION CENTER
Issue Date: 1/30/2026
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: IRiS
Catalog Number: P3AS13R60W2N902765DE010 E3DLP1GPH_3000K
Description: 3in Adjustable Tunable White LED luminaire with, R60 optic, 3000K CCT AND, 90CRI ,
E3DLP1GPH TRIM
Light Source: -
Ballast/Driver: -


Summary

Lumens per Lamp: N/A
Luminaire Lumens: 272.0 lumens
Efficiency: N/A
Efficacy: 22.1 lumens/watt
Spacing Criteria (0/90/45): 0.79 / 0.79 / 0.83
Luminous Opening: Circular (Dia: 0.25' x H: 0')
CIE Type: Direct

Input Watts (W): 12.3
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT

TEST NUMBER: P1298473
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLP1GPH_3000K

Luminous Intensity Polar Plot





TEST NUMBER: P1298473

CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLP1GPH_3000K

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	28.5	10.5
10°-20°	69.2	25.5
20°-30°	76.0	27.9
30°-40°	55.3	20.3
40°-50°	26.1	9.6
50°-60°	8.6	3.1
60°-70°	4.9	1.8
70°-80°	2.6	1.0
80°-90°	0.8	0.3
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	173.7	63.9
0°-40°	229.0	84.2
0°-60°	263.7	97.0
0°-90°	272.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	272.0	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	314	
5°	306	28
15°	249	69
25°	166	76
35°	88	55
45°	33	26
55°	9	9
65°	5	5
75°	3	3
85°	1	1
90°	0	



TEST NUMBER: P1298473
CATALOG NUMBER: P3AS13R60W2N902765DE010 E3DLP1GPH_3000K

CANDELA DISTRIBUTION (FULL):

	0°
0°	314.4
2.5°	312.5
5°	306.1
7.5°	296.4
10°	283.3
12.5°	267.6
15°	249.3
17.5°	229.5
20°	208.6
22.5°	187.3
25°	166.3
27.5°	145.4
30°	125.6
32.5°	106.5
35°	88.2
37.5°	71.8
40°	56.8
42.5°	43.7
45°	32.9
47.5°	23.9
50°	16.4
52.5°	10.8
55°	8.6
57.5°	7.5
60°	6.7
62.5°	5.6
65°	4.9
67.5°	4.1
70°	3.4
72.5°	3.0
75°	2.6
77.5°	1.9
80°	1.5
82.5°	1.1
85°	0.7
87.5°	0.4
90°	0.0

(END OF REPORT)